





Ultrasonic cleaning units

Transsonic TI-H

Multi-frequency units for industrial applications

- Robust and durable ultrasonic cleaning units with individually adjustable multi-frequency for intensive and gentle cleaning tasks
- Degas-function for fast and efficient degassing of new cleaning liquids
- Sweep-function for an excellent sound field distribution and even better cleaning results

Transsonic TI-H

The ultrasonic cleaning units with multi-frequency for the industry

Adjustable multi-frequencies for different cleaning task

- Multi-frequency version with 25/45 kHz:
 - 25 kHz for the coarse removal of lapping abrasives and polishing media.
 - 45 kHz for the fine cleaning of oils and grease.
- Multi-frequency version with 35/130 kHz:
 - 35 kHz for the removal of oils and grease from hard surfaces made of metal, glass and hard precious stones.
 - 130 kHz for the cleaning of sensitive surfaces, e.g. in the jewellery business and for electronic parts.

Ultrasonic technology with thoughtout functions

Degas-function

Newly prepared cleaning fluid is saturated with air. The gas should be removed from the fluid in order to optimise its effectiveness in an ultrasonic bath. This is easily accomplished with the Degas-function. Furthermore the function is used for the degassing of HPLC solvents in the industrial laboratory.

Sweep-function

The Sweep-function creates a uniform sound field distribution and thus the cleaning power is optimum distributed throughout the entire cleaning bath.







Stainless steel basket, stainless steel cover, hinged noise protection cover, and much more.

Technical data

	TI-H-5	TI-H-10	TI-H-15	TI-H-20
Ultrasonic frequency* (kHz)	25/45 or 35/130	25/45 or 35/130	25/45 or 35/130	25/45 or 35/130
Tank operating capacity (I)	3.5	8.6	12.2	16.8
Max. tank capacity (I)	4.7	10.8	14.4	19.8
Ultrasonic power effective (W)	100	200	200	250
Heating power (W)	400	800	1000	1400
Unit external dimensions W/D/H (mm)	340 / 300 / 370	400 / 415 / 370	400 / 415 / 420	430 / 470 / 420
Tank internal dimensions W/D/H (mm)	240 / 130 / 150	300 / 240 / 150	300 / 240 / 200	330 / 300 / 200
Max. basket loading (kg)	3.0	7.0	7.0	10.0
Basket internal dimensions W/D/H (mm)	200 / 100 / 90	260 / 210 / 90	260 / 210 / 135	290 / 270 / 135
Weight (kg)	10.5	14.8	16.0	20.0

*Multi frequency versions: MF2 with 25/45 kHz or MF3 with 35/130 kHz

Subject to technical and optical changes. • Transsonic TI-H_EN_02_



Ultrasonics.Steam.Ultraclean.